

## Han-Fast Lock 10mm<sup>2</sup> Ag Ro 2300St.

	Part number 09 08 000 6924 Specification Han-Fast Lock 10mm <sup>2</sup> Ag Ro 2300St.
--	---

### Identification

Category	Contacts
Series	Han-Fast <sup>®</sup> Lock
Type of contact	PCB contact
Description of the contact	Without pin

### Version

Pack contents	2300 pieces on reel
---------------	---------------------

### Technical characteristics

Conductor cross-section	10 mm <sup>2</sup>
Rated current	≤60 A
Contact resistance	≤2 mΩ
Stripping length	7.5 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (locking)	Copper alloy
Surface (locking)	Passivated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



## Material properties

REACH SVHC substances Not contained

California Proposition 65 substances Yes

## Specifications and approvals

UL / CSA UL 1977 ECBT2.E235076  
CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	1
Net weight	6,120 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140014855
ETIM	EC002637
eCl@ss	27460201 PCB connector (board connector)