

## Han TC300 male contact 70mm<sup>2</sup>



Image is for illustration purposes only. Please refer to product description.

Part number	09 11 000 7535
Specification	Han TC300 male contact 70mm <sup>2</sup>
HARTING eCatalogue	<a href="https://harting.com/09110007535">https://harting.com/09110007535</a>

### Identification

Category	Contacts
Series	TC 300
Type of contact	Crimp contact

### Version

Termination method	Crimp termination
Gender	Male
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	70 mm <sup>2</sup>
Rated current	≤300 A
Contact resistance	≤0.3 mΩ
Stripping length	24 mm
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance  
Since 1945

## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
California Proposition 65 substances	Not contained

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	2
Net weight	37.5 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140188389
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522