

Han TC100-HMC-FC-CRT-25 mm²-AU



Image is for illustration purposes only. Please refer to product description.

Part number	09 11 200 6225
Specification	Han TC100-HMC-FC-CRT-25 mm ² -AU
HARTING eCatalogue	https://harting.com/09112006225

Identification

Category	Contacts
Series	TC 100
Type of contact	Crimp contact

Version

Termination method	Crimp termination
Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	25 mm ²
Rated current	≤100 A
Contact resistance	≤0.3 mΩ
Stripping length	19 mm
Limiting temperature	-40 ... +125 °C
Mating cycles	≥10,000
Note on the mating cycles	Mating cycles with other HMC components

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	HMC gold plated



Pushing Performance
Since 1945

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	10
Net weight	15.1 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140188297
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522