

## Han TC70-HMC-FC-CRT-16mm<sup>2</sup>-AU



Part number	09 11 200 6232
Specification	Han TC70-HMC-FC-CRT-16mm <sup>2</sup> -AU
HARTING eCatalogue	<a href="https://harting.com/09112006232">https://harting.com/09112006232</a>

Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Contacts
Series	TC 70
Type of contact	Crimp contact

### Version

Termination method	Crimp termination
Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	16 mm <sup>2</sup>
Rated current	≤70 A
Contact resistance	≤0.3 mΩ
Stripping length	15.5 mm
Limiting temperature	-40 ... +125 °C
Mating cycles	≥10,000
Note on the mating cycles	Mating cycles with other HMC components

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	HMC gold plated

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	10
Net weight	9 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140188181
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522