

## Han-Modular coax F-contact 50Ohm (RG174)



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 000 6211
Specification	Han-Modular coax F-contact 50Ohm (RG174)
HARTING eCatalogue	<a href="https://harting.com/09140006211">https://harting.com/09140006211</a>

### Identification

Category	Contacts
Series	DIN 41626
Type of contact	Coaxial contact
Description of the contact	for cables RG 174 U, 188 AU, 316 U

### Version

Termination method	Solder/crimp termination
Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Rated current	≤1.5 A
Contact resistance	≤10 mΩ
Impedance coaxial	50 Ω

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	10
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140018341
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522