

Pneumatic contact female 4,0 mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 000 6253
Specification	Pneumatic contact female 4,0 mm
HARTING eCatalogue	https://harting.com/09140006253

Identification

Category	Contacts
Type of contact	Pneumatic contact
Description of the contact	Without shut-off Straight

Version

Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Limiting temperature	-40 ... +80 °C
Operating pressure	≤8 bar
Mating cycles	≥500
Tube inner diameter	4 mm

Material properties

Material (contacts)	Delrin acetal
Material (seal)	Buna-N
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

Material properties

REACH SVHC substances Not contained

California Proposition 65 substances Not contained

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

Commercial data

Packaging size	10
Net weight	0.24 g
Country of origin	Germany
European customs tariff number	39269097
GTIN	5713140018396
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522