

Pneum. contact metal ID 10mm, male



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 000 6310
Specification	Pneum. contact metal ID 10mm, male
HARTING eCatalogue	https://harting.com/09140006310

Identification

Category	Contacts
Type of contact	Pneumatic contact
Description of the contact	Without shut-off Straight

Version

Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Limiting temperature	-40 ... +85 °C
Operating pressure	≤10 bar
Mating cycles	≥10,000
Tube inner diameter	10 mm

Material properties

Material (contacts)	Brass
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

Material properties

REACH SVHC substances	Not contained
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Not contained

Commercial data

Packaging size	10
Net weight	35.39 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140189294
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522

