

Pneum. contact metal OD 6 male



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 000 6356
Specification	Pneum. contact metal OD 6 male
HARTING eCatalogue	https://harting.com/09140006356

Identification

Category	Contacts
Type of contact	Pneumatic contact
Description of the contact	Without shut-off Straight
Features	The Han® Pneumatic contacts without shut-off are suitable for the use inside a vacuum. (Limit: 100 mbar = 100 hPa ≈ approx 90% vacuum)

Version

Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Limiting temperature	-20 ... +85 °C
Operating pressure	≤10 bar
Mating cycles	≥10,000
Tube outer diameter	6 mm

Material properties

Material (contacts)	Brass
Material (seal)	HNBR (hydrated NBR)
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

Commercial data

Packaging size	10
Net weight	14.6 g
Country of origin	Romania
European customs tariff number	39269097
GTIN	5713140162099
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522

