

## Pneum. contact metal ID 3 female+valve



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 000 6413
Specification	Pneum. contact metal ID 3 female+valve
HARTING eCatalogue	<a href="https://harting.com/09140006413">https://harting.com/09140006413</a>

### Identification

Category	Contacts
Type of contact	Pneumatic contact
Description of the contact	With shut-off Straight

### Version

Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Limiting temperature	-40 ... +85 °C
Operating pressure	≤10 bar
Mating cycles	≥10,000
Tube inner diameter	3 mm

### Material properties

Material (contacts)	Brass
Material (seal)	HNBR (hydrated NBR)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Naphthalene

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

## Commercial data

Packaging size	10
Net weight	9 g
Country of origin	Romania
European customs tariff number	39269097
GTIN	5713140189348
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522



**Pushing Performance**  
Since 1945

