

Pneum. contact metal OD 4mm male angled



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Contacts
Type of contact	Pneumatic contact
Description of the contact	Without shut-off Angled
Features	The Han® Pneumatic contacts without shut-off are suitable for the use inside a vacuum. (Limit: 100 mbar = 100 hPa ≈ approx 90% vacuum)

Version

Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Limiting temperature	-20 ... +85 °C
Operating pressure	≤10 bar
Mating cycles	≥10,000
Tube outer diameter	4 mm

Material properties

Material (contacts)	Brass
Material (seal)	HNBR (hydrated NBR)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Naphthalene

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

Commercial data

Packaging size	10
Net weight	13 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140189157
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522