

## Han-Modular ECO agg IP65 (without PE)



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 001 0320
Specification	Han-Modular ECO agg IP65 (without PE)
HARTING eCatalogue	<a href="https://harting.com/09140010320">https://harting.com/09140010320</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han-Modular® ECO
Type of hood/housing	Bulkhead mounted housing

### Version

Size	Modular ECO
Locking type	Snap-in latches

### Technical characteristics

Limiting temperature	-40 ... +85 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 7032 (pebble grey)
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	CE

## Commercial data

Packaging size	2
Net weight	17.23 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140019003
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466