

## Han GND housing



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 001 0330
Specification	Han GND housing
HARTING eCatalogue	<a href="https://harting.com/09140010330">https://harting.com/09140010330</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han® GND
Type of hood/housing	Bulkhead mounted housing

### Version

Locking type	Snap-in latches
--------------	-----------------

### Technical characteristics

Limiting temperature	-40 ... +85 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	Green
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

## Material properties

REACH SVHC substances Not contained

California Proposition 65 substances Not contained

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	2
Net weight	16.62 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140019027
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466