

## Han pneumatic module for 2 contact, male



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 002 3501
Specification	Han pneumatic module for 2 contact, male
HARTING eCatalogue	<a href="https://harting.com/09140023501">https://harting.com/09140023501</a>

### Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® Pneumatic module
Size of the module	Double module

### Version

Gender	Male
Number of contacts	2
Details	Please order contacts separately.

### Technical characteristics

Limiting temperature	-40 ... +85 °C
Mating cycles	≥10,000

### Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	Blue
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

## Material properties

REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 61984 IEC 60664-1
----------------	--------------------------

## Commercial data

Packaging size	2
Net weight	12 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140184862
eCl@ss	27440220 Module for industrial connectors (pneumatic)
ETIM	EC000438
UNSPSC 24.0	39121552