

Han-Modular Twin Kappe



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 002 5401
Specification	Han-Modular Twin Kappe
HARTING eCatalogue	https://harting.com/09140025401

Identification

Category	Accessories
Series of hoods/housings	Han-Modular® Twin
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings

Version

Size	Modular Twin
Locking type	Single locking lever
Details	<p>Rated voltage \leq630 V Rated impulse voltage \leq6 kV Pollution degree 3</p> <p>For a complete connector the specified voltage rating is the maximum level which can be achieved. In cases where the used module(s) do offer lower voltage ratings, then these lower ratings are valid. Higher voltage ratings in individual applications can be approved in coordination with HARTING.</p>

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	IEC 61984
----------------	-----------

Commercial data

Packaging size	1
Net weight	60 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140019980
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467