

Han-Mod RJ45 PreLink Set 8P AWG 22-23



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Inserts
Element	Data connectors
Specification	Han® RJ45 cable jack

Version

Termination method	preLink® IDC insulation displacement termination
Gender	Female
Number of contacts	8

Technical characteristics

Conductor cross-section [AWG]	AWG 23 ... AWG 22
Wire outer diameter	1.3 ... 1.6 mm
Transmission characteristics	Cat. 6A Class E _A up to 500 MHz
	10 Mbit/s
	100 Mbit/s
Data rate	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Cable diameter	5 ... 9 mm

Material properties

Material (insert)	Polyamide (PA)
-------------------	----------------

Material properties

Material (shielding)	Zinc die-cast, nickel-plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	15 g
Country of origin	Latvia
European customs tariff number	85389099
GTIN	5713140020795
eCl@ss	27440218 Module for industrial connectors (data)
ETIM	EC000438
UNSPSC 24.0	39121552