

Sliding frame Han 16B, floating side



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 016 1721
Specification	Sliding frame Han 16B, floating side
HARTING eCatalogue	https://harting.com/09140161721

Identification

Category	Accessories
Type of accessory	Sliding frame
Description of the accessory	with test position for 4 modules Float mount A ... D

Version

Size	16 B
------	------

Technical characteristics

Limiting temperature	-5 ... +55 °C
Mating cycles	≥500
Floating tolerance	+3 mm
Lock-in range	±4 mm

Material properties

Material	Polycarbonate (PC)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Not contained
-----------------------	---------------

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	1
Net weight	30.53 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140194519
eCl@ss	27440210 Fixing element for industrial connectors
ETIM	EC002310
UNSPSC 24.0	39121466