

Han-Mod RJ45 IDC cable jack 4P AWG 24-22



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 545 1120
Specification	Han-Mod RJ45 IDC cable jack 4P AWG 24-22
HARTING eCatalogue	https://harting.com/09145451120

Identification

Category	Inserts
Element	Data connectors
Specification	Han® RJ45 cable jack

Version

Termination method	IDC insulation displacement termination
Gender	Female
Number of contacts	4

Technical characteristics

Conductor cross-section [AWG]	AWG 24 ... AWG 22
Wire outer diameter	1.6 mm
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Cable diameter	5 ... 9 mm

Material properties

Material (insert)	Polyamide (PA)
Material (shielding)	Zinc die-cast, nickel-plated
Material flammability class acc. to UL 94	V-0

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	20 g
Country of origin	Latvia
European customs tariff number	85389099
GTIN	5713140021570
eCl@ss	27440218 Module for industrial connectors (data)
ETIM	EC000438
UNSPSC 24.0	39121552