

## Han D M Crimpkontakt 0,14-0,37mm<sup>2</sup> Fe



Part number	09 15 000 6171
Specification	Han D M Crimpkontakt 0,14-0,37mm <sup>2</sup> Fe
HARTING eCatalogue	<a href="https://harting.com/09150006171">https://harting.com/09150006171</a>

Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Contacts
Series	Han D®
Type of contact	Crimp contact

### Version

Termination method	Crimp termination
Gender	Male
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	0.14 ... 0.37 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 26 ... AWG 22
Rated current	≤10 A
Contact resistance	≤1 mΩ
Stripping length	8 mm

### Material properties

Material (contacts)	Iron
Surface (contacts)	Gold plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	25
Net weight	0.67 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140021976
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522