

## Han D F Crimpkontakt 0,5 mm<sup>2</sup> GT/SMC

	Part number	09 15 000 6403
	Specification	Han D F Crimpkontakt 0,5 mm <sup>2</sup> GT/SMC

### Identification

Category	Contacts
Series	Han D®
Type of contact	Crimp contact

### Version

Termination method	Crimp termination
Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	0.5 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 20
Rated current	≤10 A
Contact resistance	≤3 mΩ
Stripping length	8 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Han®-GoldTec
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	100
Net weight	0.64 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140022355
ETIM	EC000796
eCI@ss	27440204 Contact for industrial connectors