

## R 15-7+E-ISK-STI



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 007 3021
Specification	R 15-7+E-ISK-STI
HARTING eCatalogue	<a href="https://harting.com/09150073021">https://harting.com/09150073021</a>

### Identification

Category	Inserts
Series	R 15

### Version

Termination method	Crimp termination
Gender	Male
Number of contacts	7
Details	for metal hoods / housings

### Technical characteristics

Rated current	10 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Rated voltage acc. to UL	600 V
Rated voltage acc. to CSA	600 V
Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

### Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	RAL 7032 (pebble grey)

## Material properties

Material flammability class acc. to UL 94	HB
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Naphthalene

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

## Commercial data

Packaging size	10
Net weight	5.5 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140022683
eCl@ss	27440223 Contact insert for circular connectors
ETIM	EC003557
UNSPSC 24.0	39121421