

## M23 HBM back M3



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 15 100 0306                                                                |
| Specification      | M23 HBM back M3                                                               |
| HARTING eCatalogue | <a href="https://harting.com/09151000306">https://harting.com/09151000306</a> |

### Identification

|                             |                            |
|-----------------------------|----------------------------|
| Category                    | Hoods / Housings           |
| Series                      | Circular connectors M23    |
| Identification              | Signal                     |
| Type of hood/housing        | Panel feed through housing |
| Description of hood/housing | Rear mounting              |

### Version

|              |                                        |
|--------------|----------------------------------------|
| Size         | M23                                    |
| Fixing       | Thread 4x M3                           |
| Locking type | Screw locking<br>ComLock rapid locking |

### Technical characteristics

|                                        |                                                                          |
|----------------------------------------|--------------------------------------------------------------------------|
| Limiting temperature                   | -40 ... +125 °C                                                          |
| Degree of protection acc. to IEC 60529 | IP67 locked condition<br>IP69 / IPX9K acc. to ISO 20653 locked condition |

### Material properties

|                         |                   |
|-------------------------|-------------------|
| Material (hood/housing) | Copper-zinc alloy |
| Surface (hood/housing)  | Nickel plated     |
| Material (seal)         | NBR               |
| Colour (seal)           | Black             |
| RoHS                    | compliant         |
| ELV status              | compliant         |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                |
|--------------------------------------|----------------|
| China RoHS                           | e              |
| REACH Annex XVII substances          | Not contained  |
| REACH ANNEX XIV substances           | Not contained  |
| REACH SVHC substances                | Not contained  |
| California Proposition 65 substances | Yes            |
| California Proposition 65 substances | Lead<br>Nickel |

## Specifications and approvals

|          |                       |
|----------|-----------------------|
| UL / CSA | UL 1977 ECBT2.E235076 |
|----------|-----------------------|

## Commercial data

|                                |                                        |
|--------------------------------|----------------------------------------|
| Packaging size                 | 5                                      |
| Net weight                     | 26.546 g                               |
| Country of origin              | Germany                                |
| European customs tariff number | 85389099                               |
| GTIN                           | 5713140184169                          |
| eCl@ss                         | 27440224 Shell for circular connectors |
| ETIM                           | EC003556                               |
| UNSPSC 24.0                    | 39121405                               |