

Han F+B 5E SMC FI SCT 0,75 - 2,5 mm²



Part number	09 15 505 2701
Specification	Han F+B 5E SMC FI SCT 0,75 - 2,5 mm ²
HARTING eCatalogue	https://harting.com/09155052701

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Inserts
Series	Han [®] F+B

Version

Termination method	Screw termination
Gender	Female
With wire protection	Yes
Number of contacts	5
PE contact	Yes

Technical characteristics

Conductor cross-section	0.75 ... 2.5 mm ²
Rated current	16 A
Rated voltage	600 V
Rated impulse voltage	6 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0

Commercial data

Packaging size	1
Net weight	28.49 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140186774
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438
UNSPSC 24.0	39121522