

Han F+B cover-agg blue



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 513 5401
Specification	Han F+B cover-agg blue
HARTING eCatalogue	https://harting.com/09155135401

Identification

Category	Accessories
Series	Han® F+B
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings for cable to cable housing With fixing cord

Version

Locking type	Screw locking
Details	Cleaning: For cleaning with high pressure lances, a cleaning distance > 30 cm is recommended in order to avoid mechanical damage to the connector's exterior parts. Strain relief: A suitable strain relief is required to enable the F+B connectorto resist the stress caused e.g. by the daily cleaning of the machinery. DIN VDE 0100-520: 2013-06 defines the stress relief for a connector depending on the outer diameter of the cable.

Technical characteristics

Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP67 locked condition IP6K9K acc. to ISO 20653

Material properties

Material (hood/housing)	Polypropylen
Roughness of the surface	≤1.12 µm
Colour (hood/housing)	Blue

Material properties

Material flammability class acc. to UL 94	HB
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
EG1935/2004	compliant
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Approvals	Ecolab Topactive 200 Ecolab Topactive 500 Ecolab Topax 66 Ecolab Topactive OKTO Ecolab Topax 990 FDA 21 CFR 177.1520 FDA 21 CFR 177.2600
-----------	--

Commercial data

Packaging size	1
Net weight	13.3 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140192348
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467