

M23 P HBM Front M20x1,5



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 600 0303
Specification	M23 P HBM Front M20x1,5
HARTING eCatalogue	https://harting.com/09156000303

Identification

Category	Hoods / Housings
Series	Circular connectors M23
Identification	Power
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Straight Front mounting

Version

Size	M23
Fixing	Thread M20 x 1.5
Locking type	Screw locking
Details	Not compatible to ComLock

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 locked condition IP69 / IPX9K acc. to ISO 20653 locked condition

Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated
Material (seal)	NBR
Colour (seal)	Black
RoHS	compliant

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

Commercial data

Packaging size	5
Net weight	32.02 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140184343
eCl@ss	27440224 Shell for circular connectors
ETIM	EC003556
UNSPSC 24.0	39121405