

## M23 P female-c 1mm (0,75–1,5mm<sup>2</sup>) Au

	Part number	09 15 600 6202
Specification	M23 P female-c 1mm (0,75–1,5mm <sup>2</sup> ) Au	
HARTING eCatalogue	<a href="https://harting.com/09156006202">https://harting.com/09156006202</a>	

Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Contacts
Series	Circular connectors M23
Identification	Power
Type of contact	Crimp contact
Description of the contact	1.5 mm

### Version

Termination method	Crimp termination
Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	0.75 ... 1.5 mm <sup>2</sup>
Rated current	≤10 A
Contact resistance	≤3 mΩ
Stripping length	7 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	100
Net weight	0.34 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140189034
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522