

M23 cover-s met for hood,chain 100mm



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Accessories
Series	Circular connectors M23
Identification	Power
Type of accessory	Protection cover
Description of the accessory	for hoods With chain (100 mm)

Version

Details	Not compatible to ComLock
---------	---------------------------

Technical characteristics

Degree of protection acc. to IEC 60529	IP67 locked condition IP69 / IPX9K acc. to ISO 20653 locked condition
--	--

Material properties

Material (accessories)	Metal
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Material properties

California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

Commercial data

Packaging size	5
Net weight	8 g
Country of origin	Germany
European customs tariff number	74199990
GTIN	5713140184435
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467