

## LP-ADAPTER Han DD



Image is for illustration purposes only. Please refer to product description.

Part number	09 16 000 9905
Specification	LP-ADAPTER Han DD
HARTING eCatalogue	<a href="https://harting.com/09160009905">https://harting.com/09160009905</a>

### Identification

Category	Accessories
Type of accessory	PCB adapter
Description of the accessory	<p>In the Han DD® crimp insert</p> <p>In the Han DD® module</p> <p>In the Han® DDD module (different electrical data: 7.5 A 160 V 2.5 kV 3)</p>

### Version

Gender	Male
	Female
Details	for PCB's up to 1.6 mm

### Technical characteristics

Rated current	7.5 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Limiting temperature	-40 ... +125 °C

### Material properties

Material (insert)	Polyamide (PA)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	------------------------------------------------------------

## Commercial data

Packaging size	10
Net weight	2 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140572812
eCl@ss	27460201 PCB connector (board connector)
UNSPSC 24.0	39121415