

## PCB Adapter w/o Pin 1.6mm for Han MegaBi



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Accessories
Type of accessory	PCB adapter

### Version

Gender	Female
Details	for PCB's up to 1.6 mm

### Technical characteristics

Rated current	7.5 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Limiting temperature	-40 ... +125 °C

### Material properties

Material (insert)	Liquid crystal polymer (LCP)
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes

## Material properties

REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 61984 EN 50467
----------------	-----------------------

## Commercial data

Packaging size	10
Net weight	3.622 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140190627
eCl@ss	27460201 PCB connector (board connector)
ETIM	EC002637
UNSPSC 24.0	39121415