

SEK CAB FLAT NSH RND AWG28/7 09P 100m



Image is for illustration purposes only. Please refer to product description.

Part number	09 18 009 7011
Specification	SEK CAB FLAT NSH RND AWG28/7 09P 100m
HARTING eCatalogue	https://b2b.harting.com/09180097011

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (round)

Version

Cable length	100 m
Number of cores	9
Core structure	AWG 28/7
Shielding	Unshielded

Technical characteristics

Limiting temperature	-30 ... +105 °C unmoved
	-20 ... +105 °C moved
Conductor resistance @ 20 °C	≤225 Ω/km
Signal run time @ 20 °C	≤5.25 ns/m
Impedance @ 100 MHz	75 Ω

Material properties

Material (cable)	PVC
Colour (cable)	Grey
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	1
Net weight	4,213 g
Country of origin	USA
European customs tariff number	85444993
GTIN	5713140024281
ETIM	EC003249
eCl@ss	27061801 Data and communication cable (copper)