

SEK CAB FLAT SH RND AWG28/7 50P 100m



Image is for illustration purposes only. Please refer to product description.

Part number	09 18 050 7010
Specification	SEK CAB FLAT SH RND AWG28/7 50P 100m
HARTING eCatalogue	https://b2b.harting.com/09180507010

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (round)

Version

Cable length	100 m
Number of cores	50
Core structure	AWG 28/7
Shielding	Shielded

Technical characteristics

Impedance	100 Ω
Limiting temperature	-30 ... +75 °C unmoved -20 ... +75 °C moved
Conductor resistance @ 20 °C	≤216 Ω/km

Material properties

Material (cable)	PVC
Colour (cable)	Grey
RoHS	compliant
ELV status	compliant
China RoHS	e



Material properties

REACH Annex XVII substances	Not contained
-----------------------------	---------------

REACH ANNEX XIV substances	Not contained
----------------------------	---------------

REACH SVHC substances	Not contained
-----------------------	---------------

Specifications and approvals

Specifications	UL 1581 UL PLCC, CL2
----------------	-------------------------

Approvals	CE
-----------	----

Commercial data

Packaging size	1
----------------	---

Net weight	30,300 g
------------	----------

Net weight	180 g/m
------------	---------

Country of origin	USA
-------------------	-----

European customs tariff number	85444993
--------------------------------	----------

GTIN	5713140025318
------	---------------

ETIM	EC003249
------	----------

eCl@ss	27061801 Data and communication cable (copper)
--------	--