

SEK CAB FLAT SH RND AWG28/7 60P 100m



Image is for illustration purposes only. Please refer to product description.

Part number	09 18 060 7010
Specification	SEK CAB FLAT SH RND AWG28/7 60P 100m
HARTING eCatalogue	https://b2b.harting.com/09180607010

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (round)

Version

Cable length	100 m
Number of cores	60
Core structure	AWG 28/7
Shielding	Shielded

Technical characteristics

Impedance	100 Ω
Limiting temperature	-30 ... +75 °C unmoved -20 ... +75 °C moved
Conductor resistance @ 20 °C	≤216 Ω/km

Material properties

Material (cable)	PVC
Colour (cable)	Grey

Specifications and approvals

Specifications	UL 1581 UL PLCC, CL2
----------------	-------------------------



Specifications and approvals

Approvals	CE
-----------	----

Commercial data

Packaging size	1
Net weight	19,640 g
Net weight	214 g/m
Country of origin	USA
European customs tariff number	85444991
GTIN	5713140025417
ETIM	EC003249
eCl@ss	27061801 Data and communication cable (copper)