

## SEK CAB FLAT NSH RND AWG28/7 64P 30,48m



Image is for illustration purposes only. Please refer to product description.

Part number	09 18 064 7008
Specification	SEK CAB FLAT NSH RND AWG28/7 64P 30,48m
HARTING eCatalogue	<a href="https://harting.com/09180647008">https://harting.com/09180647008</a>

### Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (round)

### Version

Cable length	30.48 m
Number of cores	64
Core structure	AWG 28/7
Shielding	Unshielded

### Technical characteristics

Impedance	100 Ω
Limiting temperature	-30 ... +75 °C unmoved -20 ... +75 °C moved
Conductor resistance @ 20 °C	≤216 Ω/km

### Material properties

Material (cable)	PVC
Colour (cable)	Grey
RoHS	compliant
ELV status	compliant
China RoHS	e

## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Specifications	UL 1581 UL PLCC, CL2
Approvals	CE

## Commercial data

Packaging size	1
Net weight	5,918 g
Net weight	176 g/m
Country of origin	USA
European customs tariff number	85444993
GTIN	5713140025486
eCl@ss	27061801 Data and communication cable (copper)
ETIM	EC003249
UNSPSC 24.0	26121609