

SEK-18 ACC.STRAIN RELIEF CLAMP FE 06P



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 18 506 9002 |
| Specification | SEK-18 ACC.STRAIN RELIEF CLAMP FE 06P |
| HARTING eCatalogue | https://harting.com/09185069002 |

Identification

| | |
|-------------------|---------------------|
| Category | Accessories |
| Series | SEK |
| Type of accessory | Strain relief clamp |

Version

| | |
|------|---------|
| Size | 6 poles |
|------|---------|

Material properties

| | |
|--------------------------------------|----------------------|
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Not contained |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels | R26 |

Commercial data

| | |
|--------------------------------|----------|
| Packaging size | 100 |
| Net weight | 0.003 g |
| Country of origin | Romania |
| European customs tariff number | 85389099 |



Pushing Performance
Since 1945

Commercial data

| | |
|-------------|--|
| GTIN | 5713140026650 |
| eCl@ss | 27440292 Connector component (accessories) |
| ETIM | EC002943 |
| UNSPSC 24.0 | 39121400 |