

## SEK-18 ACC.STRAIN RELIEF CLAMP FE 10P



Image is for illustration purposes only. Please refer to product description.

Part number	09 18 510 9002
Specification	SEK-18 ACC.STRAIN RELIEF CLAMP FE 10P
HARTING eCatalogue	<a href="https://harting.com/09185109002">https://harting.com/09185109002</a>

### Identification

Category	Accessories
Series	SEK
Type of accessory	Strain relief clamp

### Version

Size	10 poles
------	----------

### Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

### Commercial data

Packaging size	100
Net weight	0.25 g
Country of origin	Romania
European customs tariff number	85389099



**Pushing Performance**  
Since 1945

## Commercial data

GTIN	5713140027657
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400