

Han 3A-AK-Dichtung,Kappe o. glatt



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 003 5408
Specification	Han 3A-AK-Dichtung,Kappe o. glatt
HARTING eCatalogue	https://harting.com/09200035408

Identification

Category	Accessories
Series of hoods/housings	Han A [®]
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings for surface mounted housings With seal

Version

Size	3 A
Locking type	Single locking lever
Details	for mounted female insert or for mounted Han-Brid [®] insert

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 7032 (pebble grey)
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0



Pushing Performance
Since 1945

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	10
Net weight	3.6 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140038899
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467