

## Han 3A-AK



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 20 003 5428                                                                |
| Specification      | Han 3A-AK                                                                     |
| HARTING eCatalogue | <a href="https://harting.com/09200035428">https://harting.com/09200035428</a> |

### Identification

|                              |                                                |
|------------------------------|------------------------------------------------|
| Category                     | Accessories                                    |
| Series of hoods/housings     | Han A <sup>®</sup>                             |
| Type of accessory            | Protection cover                               |
| Description of the accessory | for cable to cable housing<br>With fixing cord |

### Version

|              |                      |
|--------------|----------------------|
| Size         | 3 A                  |
| Locking type | Single locking lever |

### Technical characteristics

|                                        |                                                    |
|----------------------------------------|----------------------------------------------------|
| Limiting temperature                   | -40 ... +125 °C                                    |
| Degree of protection acc. to IEC 60529 | IP44<br>IP65 / IP67 with seal screw 09 20 000 9918 |
| Type rating acc. to UL 50 / UL 50E     | 12                                                 |

### Material properties

|                             |               |
|-----------------------------|---------------|
| Material (hood/housing)     | Metal         |
| RoHS                        | compliant     |
| ELV status                  | compliant     |
| China RoHS                  | e             |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances  | Not contained |
| REACH SVHC substances       | Not contained |



**Pushing Performance**  
Since 1945

Material properties

|                                      |                                     |
|--------------------------------------|-------------------------------------|
| California Proposition 65 substances | Yes                                 |
| California Proposition 65 substances | Lead<br>Nickel                      |
| Fire protection on railway vehicles  | EN 45545-2 (2020-08) + A1 (2023-10) |
| Requirement set with Hazard Levels   | R1 (HL 1-3)<br>R7 (HL 1-3)          |

Specifications and approvals

|           |        |
|-----------|--------|
| Approvals | DNV GL |
|-----------|--------|

Commercial data

|                                |                                        |
|--------------------------------|----------------------------------------|
| Packaging size                 | 10                                     |
| Net weight                     | 22.6 g                                 |
| Country of origin              | Germany                                |
| European customs tariff number | 85389099                               |
| GTIN                           | 5713140038967                          |
| eCl@ss                         | 27440208 Cap for industrial connectors |
| ETIM                           | EC002314                               |
| UNSPSC 24.0                    | 39121467                               |