

## Han 3A-C/P-f.Hood--DL-grey-w.cord



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 003 5442
Specification	Han 3A-C/P-f.Hood--DL-grey-w.cord
HARTING eCatalogue	<a href="https://harting.com/09200035442">https://harting.com/09200035442</a>

### Identification

Category	Accessories
Series of hoods/housings	Han A <sup>®</sup>
Type of accessory	Protection cover
Description of the accessory	for hoods With fixing cord

### Version

Size	3 A
Locking type	Single locking lever
Details	for mounted male insert

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 7032 (pebble grey)
Material (locking)	Polyamide (PA)
Colour (locking)	RAL 7032 (pebble grey)



**Pushing Performance**  
Since 1945

## Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	10
Net weight	9.52 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140038981
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467