

Han 4B-CM-for HBM/HSM-cord, lug




Image is for illustration purposes only. Please refer to product description.

Part number	09 20 004 5425
Specification	Han 4B-CM-for HBM/HSM-cord, lug
HARTING eCatalogue	https://harting.com/09200045425

Identification

Category	Accessories
Series of hoods/housings	Han® B
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings With fixing cord (cable shoe)

Version

Size	4 B
Locking type	Single locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Metal
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	42.08 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467