

Han 4B-CM-for HBM/HSM



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 004 5432
Specification	Han 4B-CM-for HBM/HSM
HARTING eCatalogue	https://harting.com/09200045432

Identification

Category	Accessories
Series of hoods/housings	Han [®] B
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings

Version

Size	4 B
Locking type	Single locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Metal
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Not contained
--------------------------------------	---------------

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	30 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467