

## Han 6B cover plastic/SL/HBM, HSM, HCC



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 006 5405
Specification	Han 6B cover plastic/SL/HBM, HSM, HCC
HARTING eCatalogue	<a href="https://harting.com/09300065405">https://harting.com/09300065405</a>

### Identification

Category	Accessories
Series of hoods/housings	Han® B
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings for surface mounted housings

### Version

Size	6 B
Locking type	Single locking lever

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Thermoplastic
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

## Material properties

REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	14 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140161603
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467