

## Han 10B Protect Cover Die Cast



Image is for illustration purposes only. Please refer to product description.

### Identification

|                              |                               |
|------------------------------|-------------------------------|
| Category                     | Accessories                   |
| Series of hoods/housings     | Han® B                        |
| Type of accessory            | Protection cover              |
| Description of the accessory | for hoods<br>With fixing cord |

### Version

|                |                      |
|----------------|----------------------|
| Size           | 10 B                 |
| Locking type   | Double locking lever |
| Han-Easy Lock® | Yes                  |

### Technical characteristics

|  |                 |
|--|-----------------|
| Limiting temperature                   | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP65            |
| Type rating acc. to UL 50 / UL 50E     | 4<br>4X<br>12   |

### Material properties

|                         |                                       |
|-------------------------|---------------------------------------|
| Material (hood/housing) | Metal                                 |
| Material (seal)         | NBR                                   |
| Material (locking)      | Polycarbonate (PC)<br>Stainless steel |
| Colour (locking)        | RAL 7037 (dust grey)                  |

## Material properties

|  |   |
|--|---|
| Material flammability class acc. to UL 94 (locking levers) | V-0   |
| RoHS   | compliant   |
| ELV status   | compliant   |
| China RoHS   | e   |
| REACH Annex XVII substances                                | Not contained   |
| REACH ANNEX XIV substances                                 | Not contained   |
| REACH SVHC substances                                      | Yes   |
| REACH SVHC substances                                      | Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate |
| ECHA SCIP number   | 60b1a572-bb3f-476f-9307-b7d1688bd90c                      |
| California Proposition 65 substances                       | Yes   |
| California Proposition 65 substances                       | Lead<br>Nickel  |
| Fire protection on railway vehicles                        | EN 45545-2 (2020-08)                                      |
| Requirement set with Hazard Levels                         | R22 (HL 1-3)<br>R23 (HL 1-3)                              |

## Specifications and approvals

|           |        |
|-----------|--------|
| Approvals | DNV GL |
|-----------|--------|

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1                                      |
| Net weight                     | 31 g                                   |
| Country of origin              | Germany                                |
| European customs tariff number | 85389099                               |
| GTIN                           | 5713140045347                          |
| eCl@ss                         | 27440208 Cap for industrial connectors |
| ETIM                           | EC002314                               |
| UNSPSC 24.0                    | 39121467                               |