

Han 24B Docking Frame IP67 floating



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 024 1711
Specification	Han 24B Docking Frame IP67 floating
HARTING eCatalogue	https://harting.com/09300241711

Identification

Category	Accessories
Type of accessory	Docking frame

Version

Size	24 B
Details	<p>Pull-in-range x-axis: ± 1 mm</p> <p>Pull-in-range y-axis: ± 1 mm</p> <p>Pull-in-range z-axis: - 0.5 / +1 mm</p>
Pack contents	<p>1 frame</p> <p>4 cheese head shoulder screws (Steel, zinc plated) to fix the docking frame</p> <p>IP protected frame</p>

Technical characteristics

Mating cycles	$\geq 10,000$
Note on the mating cycles	Mating cycles with other HMC components
Degree of protection acc. to IEC 60529	IP65 / IP67

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (accessories)	Stainless steel

Commercial data

Packaging size	1
----------------	---

Page 1 / 2 | Creation date 2025-10-09 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electric Stiftung & Co. KG | Wilhelm-Hartung-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Commercial data

Net weight	233 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140445130
eCl@ss	27440206 Module carrier frame for industrial connectors
ETIM	EC002312
UNSPSC 24.0	39121421