

Han 48B-HBM-SL-CP



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 048 0321
Specification	Han 48B-HBM-SL-CP
HARTING eCatalogue	https://harting.com/09300480321

Identification

Category	Hoods / Housings
Series of hoods/housings	Han® B
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	With thermo-plastic cover incl. flat seal
Type	Low construction

Version

Size	48 B
Locking type	Single locking lever
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Tightening torque	3 Nm Fixing screws M6
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65
	4
Type rating acc. to UL 50 / UL 50E	4X
	12

Material properties

Material (hood/housing)	Aluminium die-cast
-------------------------	--------------------

Material properties

Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

Specifications and approvals

Approvals	CE DNV GL
-----------	--------------

Commercial data

Packaging size	1
Net weight	654 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140165502
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466