

Han E M Crimp Contact Au 0.14-0.37 mm²



Image is for illustration purposes only. Please refer to product description.

Part number	09 33 000 6117
Specification	Han E M Crimp Contact Au 0.14-0.37 mm ²
HARTING eCatalogue	https://harting.com/09330006117

Identification

Category	Contacts
Series	Han E [®]
Type of contact	Crimp contact

Version

Termination method	Crimp termination
Gender	Male
Contact identification	No groove
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.14 ... 0.37 mm ²
Conductor cross-section [AWG]	AWG 26 ... AWG 22
Rated current	≤16 A
Contact resistance	≤1 mΩ
Stripping length	7.5 mm

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



Pushing Performance
Since 1945

Material properties

China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

Commercial data

Packaging size	100
Net weight	1 g
Country of origin	Switzerland
European customs tariff number	85366990
GTIN	5713140049772
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522