

## Han E Crimp Contact-M-26-22AWG Fe(Au)



Image is for illustration purposes only. Please refer to product description.

Part number	09 33 000 6173
Specification	Han E Crimp Contact-M-26-22AWG Fe(Au)
HARTING eCatalogue	<a href="https://harting.com/09330006173">https://harting.com/09330006173</a>

### Identification

Category	Contacts
Series	Han E <sup>®</sup>
Type of contact	Crimp contact

### Version

Termination method	Crimp termination
Gender	Male
Contact identification	acc. to IEC 60584 type J
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	0.14 ... 0.37 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 26 ... AWG 22
Rated current	≤16 A
Contact resistance	≤1 mΩ
Stripping length	7.5 mm

### Material properties

Material (contacts)	Iron
Surface (contacts)	Gold plated
RoHS	compliant
ELV status	compliant
China RoHS	e



**Pushing Performance**  
Since 1945

## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	25
Net weight	1.263 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140049888
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522