

## Han E Female Contact 26-22AWG Constantan



Image is for illustration purposes only. Please refer to product description.

Part number	09 33 000 6263
Specification	Han E Female Contact 26-22AWG Constantan
HARTING eCatalogue	<a href="https://harting.com/09330006263">https://harting.com/09330006263</a>

### Identification

Category	Contacts
Series	Han E <sup>®</sup>
Type of contact	Crimp contact

### Version

Termination method	Crimp termination
Gender	Female
Contact identification	acc. to IEC 60584 type J
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	0.14 ... 0.37 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 26 ... AWG 22
Rated current	≤16 A
Contact resistance	≤1 mΩ
Stripping length	7.5 mm

### Material properties

Material (contacts)	Constantan
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	25
Net weight	1.6 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140050112
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522