

Han PushPull PFT metal rectangular HIFF



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 35 012 0311 |
| Specification | Han PushPull PFT metal rectangular HIFF |
| HARTING eCatalogue | https://harting.com/09350120311 |

Identification

| | |
|-----------------------------|-------------------------------|
| Category | Connectors |
| Series | Han® PushPull (V14) |
| Type of hood/housing | Bulkhead mounted housing |
| Description of hood/housing | for rectangular panel cut out |

Version

| | |
|--------------|----------|
| Locking type | PushPull |
|--------------|----------|

Technical characteristics

| | |
|--|----------------|
| Limiting temperature | -40 ... +70 °C |
| Mating cycles | ≥500 |
| Degree of protection acc. to IEC 60529 | IP65 IP67 |

Material properties

| | |
|---|---------------|
| Material (hood/housing) | Zinc die-cast |
| Surface (hood/housing) | Nickel plated |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |

Material properties

| | |
|--------------------------------------|----------------|
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead Nickel |

Specifications and approvals

| | |
|----------------|-------------------------------|
| Specifications | IEC 61076-3-117 EN 45545-2 |
| UL / CSA | UL 1977 ECBT2.E102079 |
| PROFINET | Yes |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 21 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140053915 |
| eCl@ss | 27440202 Shell for industrial connectors |
| ETIM | EC000437 |
| UNSPSC 24.0 | 39121466 |