

## Han PushPull PFT plastic HIFF



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 012 0331
Specification	Han PushPull PFT plastic HIFF
HARTING eCatalogue	<a href="https://harting.com/09350120331">https://harting.com/09350120331</a>

### Identification

Category	Connectors
Series	Han® PushPull (V14)
Type of hood/housing	Bulkhead mounted housing

### Version

Locking type	PushPull
Details	for all HIFF compatible modules

### Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP67

### Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

## Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Specifications	IEC 61076-3-117 EN 45545-2
UL / CSA	UL 1977 ECBT2.E102079
PROFINET	Yes

## Commercial data

Packaging size	1
Net weight	5.96 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140053939
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466