

## Han 3HPR-C-SL-W/O cord-black chrome



Image is for illustration purposes only. Please refer to product description.

Part number	09 40 003 5411
Specification	Han 3HPR-C-SL-W/O cord-black chrome
HARTING eCatalogue	<a href="https://harting.com/09400035411">https://harting.com/09400035411</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> HPR
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings for surface mounted housings

### Version

Size	3 A
Locking type	Screw locking

### Technical characteristics

Tightening torque (screw locking)	2 Nm
Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Black chrome coating
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Stainless steel



Pushing Performance  
Since 1945

## Material properties

RoHS	not compliant
ELV status	not compliant
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

## Commercial data

Packaging size	10
Net weight	47.364 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140057159
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467