

Han 16 HPR Cover Toggle Locking



Image is for illustration purposes only. Please refer to product description.

Part number	09 40 016 5401
Specification	Han 16 HPR Cover Toggle Locking
HARTING eCatalogue	https://harting.com/09400165401

Identification

Category	Accessories
Series of hoods/housings	Han [®] HPR
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings for surface mounted housings

Version

Size	16 B
Locking type	Toggle locking

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 IP68
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Stainless steel
RoHS	compliant



Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	55 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140057784
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467